EnviQ®RF

Reinforced Fiber Ultrafiltration Membranes



HOW EnviQ RF WORKS

QUA's EnviQ Membranes have been specially designed to improve the ease of operation and maintenance of MBR facilities. EnviQ provides consistent ultrafiltration quality effluent using a strong and rugged PVDF hollow fiber membrane and unique airflow distribution system. EnviQ RF membranes are manufactured using QUA's innovative Non-solvent Induced Phase Separation (NIPS) process. EnviQ RF's reinforced PVDF membrane fibers offer high mechanical strength and high chemical and chlorine tolerance. This improves the modules' ability to handle high feed turbidity for a wide range of challenging wastewater applications.

ADVANTAGES

Reinforced, Robust Hollow Fiber Membrane

 High tensile and mechanical strength membrane can handle high MLSS feed water with ease

Backwashable Membrane

Sustainable transmembrane pressure during operation

Compact and Adaptable Design

 High product flow in a small footprint, with a flexible design that withstands variable feed water

High Quality Product Water

Provides ultrafiltration quality water with >99% TSS reduction

Unique Dual Airflow Distribution System

Optimizes power consumption and reduces cleaning requirement

Complete Assembled Module

 Includes air header, product header, diffusers, frames, connectors and membrane.



THE TECHNOLOGY OF CHOICE

In addition to simpler operations, EnviQ lowers the total installed cost of biological wastewater treatment and recycle systems as compared to conventional activated sludge processes with tertiary filtration. EnviQ facilitates increased MBR adoption, resulting in more efficient biological treatment, smaller footprint and high quality effluent.



MBR combines conventional activated sludge technology with membrane filtration. MBR can be designed at a much higher mixed liquor suspended solids (MLSS) concentration compared to conventional processes, giving advantages of lower hydraulic retention time (HRT) and higher sludge retention time (SRT). In addition, MBR replaces clarifier/sedimentation tanks as well as media filtration. This reduces the footprint of the overall wastewater treatment.

The treated water is highly superior and can be used directly, or as feed to a reverse osmosis unit. EnviQ is available for a wide range of challenging wastewater applications in domestic, sewage, industrial and commercial installations.



EnviQ®RF





EnviO® RF MODULE SPECIFICATIONS

LIIVIQ	INI MICE	OLL 3	<u> </u>	10/11	10113					
			EnviQ ® RF MBR Model							
		RF-120	RF-150	RF-180	RF-210	RF-280	RF-350	RF-420	RF-490	RF-1900
Pore Size		0.04μ								
Membrane Type		Hydrophilic PVDF, Hollow Fiber Outside - In								
Membrane pH Tolerance		2-10								
Membrane Temperature Tolerance #1		5 - 40 °C / 41 - 104 °F								
Total membrane Area m ²		120	150	180	210	280	350	420	490	1900
Single cartridge Area m²		3.0 7.0								
Number of Membrane Cartridges		40	50	60	70	40	50	60	70	272
Flow m³/hr (gpm)	Minimum	1.2 (5.3)	1.5 (6.6)	1.8 (7.9)	2.1 (9.2)	2.8 (12.3)	3.5 (15.4)	4.2 (18.5)	4.9 (21.6)	19 (84)
	Maximum	3.6 (15.9)	4.5 (19.8)	5.4 (23.8)	6.3 (27.7)	8.4 (37)	10.5 (46.2)	12.6 (55.4)	14.7 (64.7)	57 (251)
Air Flow m³/hr #2 (CFM)		38 – 72 (22 – 42)	48 – 90 (28 – 53)	58 – 108 (34 – 64)	67 – 126 (39 – 74)	45 – 84 (26 – 49)	56 –105 (33 – 62)	67.2 – 126 (39 – 74)	78.4 – 147 (46 – 87)	304 – 570 (179 – 336)
Dim	ensions									
Dimensions	Length mm (inch)	893 (35.1)	1021 (40.2)	1132 (44.6)	1254 (49.4)	893 (35.2)	1021(40.2)	1132 (44.6)	1254 (49.4)	2526 (99.5)
	Width mm (inch)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1365 (53.7)	1630 (64.2)
	Height mm (inch)	1915 (75.4)	1915 (75.4)	1915 (75.4)	1915 (75.4)	3065 (120.7)	3065 (120.7)	3065 (120.7)	3065 (120.7)	3170 (124.8)
Module Weight (Dry) kgs (lbs)		322 (709.9)	380 (837.8)	440 (970.0)	495 (1091.3)	428 (943.6)	505 (1113.3)	584 (1287.5)	662 (1459.5)	2300 (5071)
Connection Flange										
Permeate		3" ASTM	3" ASTM	3" ASTM	3" ASTM	4" ASTM	4" ASTM	4" ASTM	4" ASTM	6" ASTM
Air Diffuser		1" ASTM	1" ASTM	1" ASTM	1" ASTM	1" ASTM	1" ASTM	1" ASTM	1" ASTM	2.5" ASTM
No. of Air Diffusers		8	10	12	14	8	10	12	14	34
Permeate Header Material		UPVC SS 316								
Outer Frame Material		SS 316								
Air Diffuser Type & Material		Coarse Bubble, PVC								
T () ()	ango for the biological active clude	- 1- 20 27 90								

Technical Information

Operational Parameters	UOM	Value				
MLSS	mg/L	3,000 – 15,000				
Operating pH Range	-	5 to 9				
Filtration						
Flux Range	Lmh/ gfd	10 - 30 / 6 - 17.6 *3 (dependent on feed conditions)				
Operating Transmembrane Pressure	mmHg / Psi	100 – 200 / 1.9 – 3.9				
Maximum Transmembrane Pressure	mmHg / Psi	350 / 6.8				
Filtration time	Min	5 – 30				
Rest Time	Sec	20 – 120				
Backwash						
Maximum Backwash Pressure	psi(bar)	8 (0.6)				
Backwash Frequency	N/A	After every 15 to 60 min				
Backwash Time	Sec	30 to 60				
Product						
Typical Product TSS	mg/L	<3				
Typical Product Turbidity	NTU	<1				
Cleaning Chemicals	•					
Maintenance Cleaning #4	N/A	NaOCI (250 ppm as Cl ₂) and Citric Acid (1000 ppm)				
Recovery Cleaning #5	N/A	NaOCI (1000 ppm as Cl ₂) and Citric Acid (1000 ppm)				

Actual flux would be dependent on the feed condition. Please consult QUA for guidance on modified air flow requirement for flux greater than 25 Lmh





³¹The optimal temperature range for the biological active sludge is 20 – 37 °C.
³²Air requirement given is for membrane scrubbing only and does not include air for the biological process.Refere EnviQ* Software for actual air requirements